DCP007-UV Process Photometer

Benefits:

- Ultra-low power UV analyzer
- High performance UV LED and/or • pulsed xenon light source
- Dual wavelength drift free operation •
- Maintenance free measurement cell
- Light source & wavelength easy to change
- NIST validation accessory

The Kemtrak DCP007-UV process analyzer is a high performance fiber optic coupled photometer for high resolution, real time, inline concentration measurement.


Unlike traditional UV process analyzers that use hot, powerful UV mercury vapor lamps to generate light energy, the DCP007-UV analyzer uses cold wavelength а specific light source. Mercury lamps quickly deplete over time while simultaneously



left: Optical filter used on a Kemtrak DCP007-UV photometer right: Eroded optical filter from a traditional hot mercury vapor lamp photometer

eroding bandpass filters required to limit light energy to the measurement wavelength required, resulting in drift and a continual need for maintenance, a problem not experienced with Kemtrak instruments. Furthermore, mercury vapor lamp instruments continuously expose the process stream to high intensity broad spectrum UV radiation, with the potential for product destruction and loss. The Kemtrak DCP007-UV process analyzer emits ultra-low power cold light exposing the sample to the exact wavelength required for measurement. Kemtrak DCP007-UV analyzers provide safe, drift free operation that maximize process yield and quality.

Mercury vapor lamps have a distinct set of wavelength peaks predominantly in the UV. These peaks limit the availability of wavelengths for measurement use. In contrast, a Kemtrak DCP007-UV process analyzer can be configured to measure from 190 nm to 1050 nm.



The proprietary dual wavelength, four channel measurement technique used in the DCP007-UV analyzer provides deep absorbance measurement to 5 AU using a 1 cm optical pathlength. A range of shorter optical path-lengths allow for even deeper absorbance and optical density measurements.





The convenient range of small-footprint, zero dead-volume hygienic measurement cells that contain no electronics or moving parts are well suited for both ordinary and hazardous area installation. Standard NIST-traceable validation filters can be used to verify analyzer performance without process interruption.




Integrated NIST validation accessory

Standard features include multiple product switching, remote zeroing and signal filtering. A built-in graphical internet based interface allows remote operation, calibration, validation and data trending using a standard web browser.

KENTRAK

www.kemtrak.com

All Kemtrak products are designed to meet the most demanding specifications are made from the highest quality materials ensure to exceptionally long life and the highest reliability possible.



Housing

Stainless steel EN 1.4301 (X5CrNi18-10), AISI 304 (V2A) Captive lid screws & external mounting brackets stainless steel 244 x 215 x 105 mm (L x W x D) IP 65 / EN 60529

Display

16 x 4 alphanumeric white on blue dot matrix LCD display

LED backgroona monimated	
Measurement updates every second	
LED 1 (green):	Power on
LED 2 (red):	System fault
LED 3 & 4 (orange):	Alarm 1 & Alarm 2

LED 5 (blue): Clean / Hold

Operation 4 push buttons

Remote HTML/Java interface (TCP/IP connection via Ethernet port)

Software Features:

- Fully automatic photometer gain switching Auto aain: Auto zero: .
 - Automatically, locally or remotely activated zero Calibration: 16 linearization tables for concentration & mA output
 - From 0 to 9999s with noise (air bubble / particle) filter Damping:
 - Memory: Nonvolatile - all data retained upon power failure Alphanumeric password protection
 - Security:

Data Logger

>17000 data points (timestamp, average, max. & min.), ring buffer Configurable log time interval 1s to 24hr

Event Logger> 16000 events, ring buffer Timestamp, alarms, zeroing, cleaning, product change, calibration & system events (power, system warning & error messages)

Automatic Cleaning Control

- Automatic cleaning sequence, triggering dedicated relay output Manual trigger or external trigger via digital input
- Configurable automatic cleaning interval, 15min to 2months Configurable cleaning duration from 0 to 9999s

0.0000 - 999999 0.0000 - 999999 s

0.0000 - 999999s

- Auto-zero after clean option Hold value after clean (to equilibrate) 0 to 9999s

2 - 99s

PID Controller Control method:

Pulse width modulated relay output or 0/4-20 mA output

Control period:	
Proportional gain:	
Integral time:	
Derivative time:	

Remote Input

- 5 x Digital input (potential free contact) for: Input 1-3: Product/range selection
- Input 4: Zero, instant zero, clean or clean & Zero
- input 5: Hold (freeze output), data log control or light source control Analogue Input (optional)

mA or 3-wire PT100 Range: -20 to 200°C (-4 to 392°F) Resolution: 0.07°C (0.126°F)

Flow Cells and Process Connections

Standard designs include DIN Flange (DIN 2633), ANSI (ASME B16.5), Tri-Clamp® (ISO 2852 & DIN 32676), Straight pipe thread (DIN ISO 228 BSP), NPT tapered pipe thread (ANSI B 1.20.1) Line size up to DN200 / 8"

Materials

Standard material stainless steel 316L (EN 1.4435 or EN 1.4404) Other materials include Titanium Gr 2, Hastelloy C-276 & C-22, Monel 400 & PTFE C25 (TFMC, carbon filled Tefton®)

Window

Sapphire (UV grade)

Surface Finish

Ra < 0.38 µm (electropolishing available on hygienic measurement cells) Elastomers

FPM (FKM, Viton®), EPDM (FDA), Silicone, FFKM (Kalrez® Spectrum 6375, Kalrez® 6230 FDA)

Operating Conditions

Ambient & process temperatures up to 275°C (527°F) Process pressure from 10 mbar to 200 bar (0,14 – 2900 psi) Operating conditions subject to material and design in use

Fibre Optic cable

- Silica core photonic fiber with Keylar® reinforced flexible LZSH coated stainless steel jacket Fully-interlocked stainless steel conduit for use above $85\,^\circ\text{C}$ ($185\,^\circ\text{F}$) Terminated with SMA 905 connectors.
- Lengths up to 100m (328 foot)

Light Source

High performance light emitting diode (LED) and/or pulsed xenon lamp Wavelength range: Full Width-Half Maximum (FWHM): 190 - 1050 nm 10 nm Central Wavelength (CWL) Accuracy: ±1nm > 20,000 hrs @ 280nm Typical light source lifetime: >100 000 hrs @ 500nm

Note: Measurement wavelengths must be factory installed.

Photometric Range 0.000 - 4.5 AU @ 280 nm, 10mm OPL 0.000 - 5.0 AU @ 500 nm, 10mm OPL

Photometric Accuracy

1.001 AU at 1 AU

Photometric Noise

±0.0001 AU at 1 AU

Linearity ± 0.5% of respective measuring range

mA Output

- x selectable 0 20mA / 4 20mA (NAMUR, max 21.6mA) Optional second mA output Galvanically isolated, tested during final inspection to 500 VDC < 0.1% Accuracy: Resolution: 0.025%
- $0 600 \, \text{Ohm}$ Load:

Relay Outputs

- 1 x 1 A 240VAC Failsafe output (active when system is ok) 2 x 1 A 240VAC User configurable (alarm, PID) 1 x 1 A 240VAC Automatic cleaning control
- Fuses: 4 x 1 A (type: MXT), max 100 Å breaking capacity LED status indicators flash when relays are active
- Fail-Safe:
- Dedicated relay output, 1 A 240 VAC
- mA output value used to signal a system fault (NAMUR <3.6mA or >21.0mA)

Network interface (remote communications): TCP/IP, 10Base-T and 100Base-TX Link Connector: RJ45

- Protocol:
- 1) HTML/Java interface using native protocol over TCP/IP
- Software: Web browser with Java version 6 or later 2) MODBUS server (slave) over TCP/IP (V1.1b3 compliant)
- Functions: (0x03, 0x04, 0x2B/0x0E conformity 0x01)

Operating Conditions

 Ambient temperature:
 0°C to +50°C (32°F to 122°F)

 Transport:
 -20°C to +70°C (-4°F to 158°F)

Power Supply 100-240 VAC, 50-60 Hz, & 22 - 30 VAC/VDC Mains fuse: 1 A (type MST), Max breaking capacity 35A

Power Consumption

25VA (max.)

Certificates

ISO 9001:2008, CE, ATEX Ex d IIB + H2 T5 IP66 Category 🐼 II 2 G (option)

NIST-Traceability

NIST-traceable validation accessory (option)

Protection IP66 / EN 60529



Kemtrak AB • Box 2940 • SE-187 29 Stockholm • Sweden sales@kemtrak.com • www.kemtrak.com

> We reserve the right to make changes without previous notice



Kemtrak is a leading manufacturer of fiber optic measuring and automation products for the process engineering industry. The Company provides tailor made solutions to meet the needs of a wide range of industries including chemical, petrochemical & offshore, pharmaceutical, food & beverage, pulp and paper and water & environment. With its headquarters in Stockholm Sweden, Kemtrak has trained representatives and support personnel globally. The main manufacturing facility in Gothenburg, Sweden is certified according to ISO 9001:2008.